

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253626

Luminaire Tested: P3AS02R559035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 104.0 lumens
Efficiency: N/A
Efficacy: 28.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253626

CATALOG NUMBER: P3AS02R559035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253626

CATALOG NUMBER: P3AS02R559035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19560
5°	19304
10°	18548
15°	17344
20°	15821
25°	14106
30°	12356
35°	10253
40°	8101
45°	5489
50°	3343
55°	1720
60°	1623
65°	1505
70°	1410
75°	1271
80°	1263
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5489 cd/sqm

TEST NUMBER: P1253626

CATALOG NUMBER: P3AS02R559035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.2	7.9
10°-20°	21.3	20.5
20°-30°	26.7	25.7
30°-40°	23.9	23.0
40°-50°	14.0	13.4
50°-60°	4.8	4.6
60°-70°	2.9	2.8
70°-80°	1.6	1.5
80°-90°	0.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	56.3	54.2
0°-40°	80.2	77.1
0°-60°	99.0	95.2
0°-90°	104.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	104.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	89	
5°	88	8
15°	76	21
25°	58	27
35°	38	24
45°	18	14
55°	4	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1253626

CATALOG NUMBER: P3AS02R559035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	89.2
2.5°	88.7
5°	87.7
7.5°	85.7
10°	83.3
12.5°	80.2
15°	76.4
17.5°	72.3
20°	67.8
22.5°	63.1
25°	58.3
27.5°	53.6
30°	48.8
32.5°	43.6
35°	38.3
37.5°	33.2
40°	28.3
42.5°	23.0
45°	17.7
47.5°	13.5
50°	9.8
52.5°	6.4
55°	4.5
57.5°	4.1
60°	3.7
62.5°	3.3
65°	2.9
67.5°	2.6
70°	2.2
72.5°	1.8
75°	1.5
77.5°	1.2
80°	1.0
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)