

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253782

Luminaire Tested: P3AS05R129035DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253782
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129035DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 273.0 lumens
Efficiency: N/A
Efficacy: 35.9 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253782

CATALOG NUMBER: P3AS05R129035DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1253782

CATALOG NUMBER: P3AS05R129035DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68		
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49		
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102185
5°	93814
10°	74748
15°	55869
20°	42424
25°	32131
30°	23776
35°	16972
40°	11622
45°	8125
50°	6925
55°	6805
60°	7061
65°	7472
70°	7565
75°	7879
80°	8587
85°	8554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 82.5°
Luminance: 9912 cd/sqm

TEST NUMBER: P1253782

CATALOG NUMBER: P3AS05R129035DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.7	13.8
10°-20°	69.0	25.3
20°-30°	61.2	22.4
30°-40°	40.0	14.7
40°-50°	21.4	7.8
50°-60°	16.2	5.9
60°-70°	13.9	5.1
70°-80°	9.6	3.5
80°-90°	3.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	167.9	61.5
0°-40°	208.0	76.2
0°-60°	245.6	90.0
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	466	
5°	426	38
15°	246	69
25°	133	61
35°	63	40
45°	26	21
55°	18	16
65°	14	14
75°	9	10
85°	3	4
90°	0	

TEST NUMBER: P1253782

CATALOG NUMBER: P3AS05R129035DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	466.0
2.5°	455.0
5°	426.2
7.5°	383.9
10°	335.7
12.5°	289.2
15°	246.1
17.5°	211.4
20°	181.8
22.5°	155.6
25°	132.8
27.5°	112.5
30°	93.9
32.5°	77.8
35°	63.4
37.5°	50.7
40°	40.6
42.5°	32.1
45°	26.2
47.5°	22.8
50°	20.3
52.5°	19.5
55°	17.8
57.5°	16.9
60°	16.1
62.5°	15.2
65°	14.4
67.5°	12.7
70°	11.8
72.5°	10.1
75°	9.3
77.5°	7.6
80°	6.8
82.5°	5.9
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)