

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253808

Luminaire Tested: P3AS05R159035DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159035DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 317.0 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253808
CATALOG NUMBER: P3AS05R159035DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1253808
 CATALOG NUMBER: P3AS05R159035DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136700
5°	126348
10°	100867
15°	76187
20°	58012
25°	44204
30°	31676
35°	20666
40°	12681
45°	7660
50°	5083
55°	3938
60°	3377
65°	2958
70°	2629
75°	2626
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7660 cd/sqm



TEST NUMBER: P1253808
 CATALOG NUMBER: P3AS05R159035DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	16.0
10°-20°	93.8	29.6
20°-30°	83.5	26.3
30°-40°	49.4	15.6
40°-50°	20.3	6.4
50°-60°	9.5	3.0
60°-70°	5.8	1.8
70°-80°	3.1	1.0
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.2	72.0
0°-40°	277.6	87.6
0°-60°	307.4	97.0
0°-90°	317.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	317.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	623	
5°	574	51
15°	336	94
25°	183	84
35°	77	49
45°	25	20
55°	10	10
65°	6	6
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1253808
CATALOG NUMBER: P3AS05R159035DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	623.4
1°	621.8
2°	617.2
3°	607.9
4°	592.5
5°	574.0
6°	553.9
7°	530.2
8°	505.5
9°	480.3
10°	453.0
12.5°	390.7
15°	335.6
17.5°	288.3
20°	248.6
22.5°	213.6
25°	182.7
27.5°	152.9
30°	125.1
32.5°	99.9
35°	77.2
37.5°	59.2
40°	44.3
42.5°	32.9
45°	24.7
47.5°	19.0
50°	14.9
52.5°	12.4
55°	10.3
57.5°	8.8
60°	7.7
62.5°	6.7
65°	5.7
67.5°	5.1
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.1
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)