

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253826

Luminaire Tested: P3AS05R209035DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209035DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 261.1 lumens
Efficiency: N/A
Efficacy: 36.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253826

CATALOG NUMBER: P3AS05R209035DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1253826

CATALOG NUMBER: P3AS05R209035DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		77	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	200817
5°	182544
10°	134912
15°	83451
20°	47651
25°	27219
30°	15268
35°	8298
40°	4551
45°	2512
50°	1467
55°	1070
60°	1009
65°	934
70°	833
75°	847
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2512 cd/sqm

TEST NUMBER: P1253826

CATALOG NUMBER: P3AS05R209035DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	27.5
10°-20°	102.5	39.3
20°-30°	53.5	20.5
30°-40°	20.7	7.9
40°-50°	6.7	2.6
50°-60°	2.7	1.0
60°-70°	1.8	0.7
70°-80°	1.1	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	227.8	87.3
0°-40°	248.5	95.2
0°-60°	257.9	98.8
0°-90°	261.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	261.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	916	
5°	829	72
15°	368	103
25°	112	54
35°	31	21
45°	8	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1253826

CATALOG NUMBER: P3AS05R209035DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	915.8
1°	914.0
2°	903.2
3°	886.5
4°	860.8
5°	829.3
6°	792.0
7°	750.6
8°	702.7
9°	656.1
10°	605.9
12.5°	481.6
15°	367.6
17.5°	275.1
20°	204.2
22.5°	151.3
25°	112.5
27.5°	83.0
30°	60.3
32.5°	43.6
35°	31.0
37.5°	22.4
40°	15.9
42.5°	11.3
45°	8.1
47.5°	5.8
50°	4.3
52.5°	3.3
55°	2.8
57.5°	2.5
60°	2.3
62.5°	2.0
65°	1.8
67.5°	1.5
70°	1.3
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)