

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253836

Luminaire Tested: P3AS05R209035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 406.0 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253836

CATALOG NUMBER: P3AS05R209035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253836

CATALOG NUMBER: P3AS05R209035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100431
5°	97733
10°	89911
15°	79138
20°	67883
25°	57027
30°	46108
35°	35068
40°	24961
45°	16467
50°	10200
55°	6690
60°	6096
65°	5604
70°	5321
75°	4829
80°	4546
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16467 cd/sqm

TEST NUMBER: P1253836

CATALOG NUMBER: P3AS05R209035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.1	10.1
10°-20°	97.1	23.9
20°-30°	107.7	26.5
30°-40°	82.2	20.2
40°-50°	42.1	10.4
50°-60°	17.3	4.3
60°-70°	10.8	2.7
70°-80°	6.1	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.9	60.6
0°-40°	328.1	80.8
0°-60°	387.4	95.4
0°-90°	406.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	406.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	458	
5°	444	41
15°	349	97
25°	236	108
35°	131	82
45°	53	42
55°	18	17
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1253836

CATALOG NUMBER: P3AS05R209035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	458.0
1°	458.5
2°	456.4
3°	453.8
4°	449.7
5°	444.0
6°	437.3
7°	430.1
8°	422.4
9°	413.1
10°	403.8
12.5°	377.0
15°	348.6
17.5°	319.8
20°	290.9
22.5°	262.0
25°	235.7
27.5°	209.4
30°	182.1
32.5°	156.3
35°	131.0
37.5°	108.8
40°	87.2
42.5°	68.6
45°	53.1
47.5°	40.2
50°	29.9
52.5°	22.2
55°	17.5
57.5°	16.0
60°	13.9
62.5°	12.4
65°	10.8
67.5°	9.3
70°	8.3
72.5°	6.7
75°	5.7
77.5°	4.6
80°	3.6
82.5°	2.6
85°	1.5
87.5°	0.5
90°	0.0

(END OF REPORT)