

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253837

Luminaire Tested: P3AS05R209035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 533.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253837
CATALOG NUMBER: P3AS05R209035DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1253837

CATALOG NUMBER: P3AS05R209035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	410077
5°	372770
10°	275501
15°	170421
20°	97332
25°	55552
30°	31169
35°	16945
40°	9275
45°	5117
50°	3002
55°	2179
60°	2017
65°	1868
70°	1667
75°	1779
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5117 cd/sqm



TEST NUMBER: P1253837
 CATALOG NUMBER: P3AS05R209035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.7	27.5
10°-20°	209.4	39.3
20°-30°	109.3	20.5
30°-40°	42.2	7.9
40°-50°	13.7	2.6
50°-60°	5.4	1.0
60°-70°	3.6	0.7
70°-80°	2.1	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.3	87.3
0°-40°	507.5	95.2
0°-60°	526.6	98.8
0°-90°	533.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1870	
5°	1694	147
15°	751	209
25°	230	109
35°	63	42
45°	16	14
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1253837
CATALOG NUMBER: P3AS05R209035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1870.1
1°	1866.5
2°	1844.4
3°	1810.4
4°	1757.9
5°	1693.5
6°	1617.3
7°	1532.9
8°	1435.0
9°	1339.8
10°	1237.3
12.5°	983.5
15°	750.7
17.5°	561.8
20°	417.1
22.5°	308.9
25°	229.6
27.5°	169.4
30°	123.1
32.5°	89.1
35°	63.3
37.5°	45.8
40°	32.4
42.5°	23.2
45°	16.5
47.5°	11.8
50°	8.8
52.5°	6.7
55°	5.7
57.5°	5.1
60°	4.6
62.5°	4.1
65°	3.6
67.5°	3.1
70°	2.6
72.5°	2.6
75°	2.1
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)