

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253863

Luminaire Tested: P3AS05R259035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 414.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253863

CATALOG NUMBER: P3AS05R259035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253863

CATALOG NUMBER: P3AS05R259035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98391
5°	96038
10°	88999
15°	79274
20°	68116
25°	57899
30°	47678
35°	37129
40°	26736
45°	16963
50°	10030
55°	6920
60°	6315
65°	5863
70°	5321
75°	4829
80°	4546
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16963 cd/sqm

TEST NUMBER: P1253863

CATALOG NUMBER: P3AS05R259035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	9.8
10°-20°	96.9	23.4
20°-30°	109.5	26.5
30°-40°	86.6	20.9
40°-50°	43.8	10.6
50°-60°	17.5	4.2
60°-70°	11.2	2.7
70°-80°	6.2	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	246.9	59.6
0°-40°	333.5	80.6
0°-60°	394.8	95.4
0°-90°	414.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	414.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	449	
5°	436	40
15°	349	97
25°	239	110
35°	139	87
45°	55	44
55°	18	18
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1253863

CATALOG NUMBER: P3AS05R259035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	448.7
1°	448.7
2°	447.2
3°	444.6
4°	441.0
5°	436.3
6°	430.7
7°	424.0
8°	416.7
9°	408.5
10°	399.7
11°	389.9
12°	380.6
13°	369.8
14°	359.5
15°	349.2
17.5°	320.3
20°	291.9
22.5°	265.1
25°	239.3
27.5°	214.0
30°	188.3
32.5°	164.0
35°	138.7
37.5°	115.5
40°	93.4
42.5°	72.7
45°	54.7
47.5°	40.7
50°	29.4
52.5°	22.2
55°	18.1
57.5°	16.5
60°	14.4
62.5°	12.9
65°	11.3
67.5°	9.8
70°	8.3
72.5°	7.2
75°	5.7
77.5°	4.6
80°	3.6
82.5°	2.6
85°	1.5
87.5°	0.5



TEST NUMBER: P1253863

CATALOG NUMBER: P3AS05R259035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)