

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253868

Luminaire Tested: P3AS05R259035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 539.0 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253868

CATALOG NUMBER: P3AS05R259035DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1253868

CATALOG NUMBER: P3AS05R259035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	345740
5°	322583
10°	258401
15°	175415
20°	106129
25°	62060
30°	35347
35°	19434
40°	10334
45°	5427
50°	3173
55°	2370
60°	2017
65°	2127
70°	1988
75°	1779
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5427 cd/sqm

TEST NUMBER: P1253868

CATALOG NUMBER: P3AS05R259035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.0	24.1
10°-20°	212.4	39.4
20°-30°	121.4	22.5
30°-40°	47.9	8.9
40°-50°	14.7	2.7
50°-60°	5.8	1.1
60°-70°	3.9	0.7
70°-80°	2.2	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	463.9	86.1
0°-40°	511.8	94.9
0°-60°	532.3	98.8
0°-90°	539.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	539.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1577	
5°	1466	130
15°	773	212
25°	256	121
35°	73	48
45°	18	15
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1253868

CATALOG NUMBER: P3AS05R259035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1576.7
1°	1573.6
2°	1560.8
3°	1538.1
4°	1506.7
5°	1465.5
6°	1417.1
7°	1362.5
8°	1299.1
9°	1234.2
10°	1160.5
11°	1087.9
12°	1008.1
13°	929.3
14°	848.4
15°	772.7
17.5°	599.1
20°	454.8
22.5°	341.5
25°	256.5
27.5°	190.1
30°	139.6
32.5°	101.0
35°	72.6
37.5°	51.5
40°	36.1
42.5°	24.7
45°	17.5
47.5°	12.4
50°	9.3
52.5°	7.2
55°	6.2
57.5°	5.7
60°	4.6
62.5°	4.1
65°	4.1
67.5°	3.6
70°	3.1
72.5°	2.6
75°	2.1
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5



TEST NUMBER: P1253868

CATALOG NUMBER: P3AS05R259035DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)