

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252850

Luminaire Tested: P3AS20R609030D010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609030D010 E3D1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2185.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252850
CATALOG NUMBER: P3AS20R609030D010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1252850
 CATALOG NUMBER: P3AS20R609030D010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81				81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71				71
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	70	68	66				66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	521756
5°	501077
10°	515889
15°	522523
20°	461387
25°	388837
30°	315365
35°	205374
40°	94320
45°	36159
50°	12110
55°	3211
60°	2982
65°	2646
70°	2180
75°	2881
80°	2147
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36159 cd/sqm



TEST NUMBER: P1252850
 CATALOG NUMBER: P3AS20R609030D010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.1	10.0
10°-20°	630.3	28.8
20°-30°	735.2	33.6
30°-40°	474.4	21.7
40°-50°	106.3	4.9
50°-60°	10.6	0.5
60°-70°	5.0	0.2
70°-80°	2.9	0.1
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1584.6	72.5
0°-40°	2059.0	94.2
0°-60°	2175.9	99.6
0°-90°	2185.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2185.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2379	
5°	2276	219
15°	2302	630
25°	1607	735
35°	767	474
45°	117	106
55°	8	11
65°	5	5
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P1252850
CATALOG NUMBER: P3AS20R609030D010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2379.4
2.5°	2340.6
5°	2276.4
7.5°	2273.0
10°	2316.9
12.5°	2345.6
15°	2301.7
17.5°	2169.9
20°	1977.2
22.5°	1776.1
25°	1607.1
27.5°	1441.5
30°	1245.5
32.5°	1015.7
35°	767.2
37.5°	523.9
40°	329.5
42.5°	197.7
45°	116.6
47.5°	67.6
50°	35.5
52.5°	11.8
55°	8.4
57.5°	6.8
60°	6.8
62.5°	5.1
65°	5.1
67.5°	5.1
70°	3.4
72.5°	3.4
75°	3.4
77.5°	1.7
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)