

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253899

Luminaire Tested: P3AS05R309035DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309035DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 332.0 lumens
Efficiency: N/A
Efficacy: 46.1 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253899
CATALOG NUMBER: P3AS05R309035DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1253899
 CATALOG NUMBER: P3AS05R309035DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	68	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113456
5°	109927
10°	99041
15°	81930
20°	63426
25°	47591
30°	34537
35°	23022
40°	14141
45°	8311
50°	5083
55°	4129
60°	3596
65°	2958
70°	2629
75°	2626
80°	1894
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8311 cd/sqm



TEST NUMBER: P1253899
 CATALOG NUMBER: P3AS05R309035DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.9	13.8
10°-20°	99.4	29.9
20°-30°	90.4	27.2
30°-40°	54.7	16.5
40°-50°	21.9	6.6
50°-60°	9.7	2.9
60°-70°	5.8	1.8
70°-80°	3.2	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	235.8	71.0
0°-40°	290.4	87.5
0°-60°	322.0	97.0
0°-90°	332.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	332.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	517	
5°	499	46
15°	361	99
25°	197	90
35°	86	55
45°	27	22
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1253899
CATALOG NUMBER: P3AS05R309035DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	517.4
1°	516.9
2°	514.8
3°	511.2
4°	506.1
5°	499.4
6°	491.1
7°	482.4
8°	471.0
9°	458.2
10°	444.8
11°	429.3
12°	412.9
13°	396.4
14°	378.4
15°	360.9
17.5°	315.1
20°	271.8
22.5°	231.7
25°	196.7
27.5°	164.7
30°	136.4
32.5°	110.2
35°	86.0
37.5°	65.9
40°	49.4
42.5°	36.0
45°	26.8
47.5°	20.1
50°	14.9
52.5°	11.8
55°	10.8
57.5°	9.3
60°	8.2
62.5°	6.7
65°	5.7
67.5°	5.1
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.6
80°	1.5
82.5°	1.0
85°	1.0
87.5°	0.5



TEST NUMBER: P1253899
CATALOG NUMBER: P3AS05R309035DE010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)