

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253912

Luminaire Tested: P3AS05R359035DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253912
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359035DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 265.1 lumens
Efficiency: N/A
Efficacy: 36.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253912

CATALOG NUMBER: P3AS05R359035DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253912

CATALOG NUMBER: P3AS05R359035DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		90
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133652
5°	128439
10°	111911
15°	85721
20°	57358
25°	34696
30°	19902
35°	11136
40°	5925
45°	3039
50°	1467
55°	1147
60°	1096
65°	934
70°	962
75°	847
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3039 cd/sqm

TEST NUMBER: P1253912

CATALOG NUMBER: P3AS05R359035DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.1	20.0
10°-20°	102.9	38.8
20°-30°	67.4	25.4
30°-40°	27.3	10.3
40°-50°	8.2	3.1
50°-60°	2.8	1.1
60°-70°	1.9	0.7
70°-80°	1.1	0.4
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.3	84.3
0°-40°	250.7	94.6
0°-60°	261.7	98.7
0°-90°	265.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	265.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	610	
5°	584	53
15°	378	103
25°	143	67
35°	42	27
45°	10	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1253912

CATALOG NUMBER: P3AS05R359035DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	609.5
1°	608.5
2°	605.7
3°	600.2
4°	593.6
5°	583.5
6°	570.9
7°	556.8
8°	540.9
9°	522.8
10°	502.6
11°	480.2
12°	456.8
13°	430.5
14°	405.6
15°	377.6
17.5°	309.8
20°	245.8
22.5°	189.1
25°	143.4
27.5°	106.9
30°	78.6
32.5°	57.7
35°	41.6
37.5°	29.5
40°	20.7
42.5°	14.4
45°	9.8
47.5°	6.6
50°	4.3
52.5°	3.3
55°	3.0
57.5°	2.8
60°	2.5
62.5°	2.3
65°	1.8
67.5°	1.5
70°	1.5
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3



TEST NUMBER: P1253912

CATALOG NUMBER: P3AS05R359035DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)