

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252934

Luminaire Tested: P3AS24R159030D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R159030D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2469.0 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252934

CATALOG NUMBER: P3AS24R159030D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1252934

CATALOG NUMBER: P3AS24R159030D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	105		104	103	102		101	100	99
2	112	109	107	105		110	108	105	103		105	103	101		102	100	99		99	98	97
3	110	106	102	100		108	104	102	99		102	100	98		100	98	96		98	96	95
4	107	102	99	96		106	101	98	96		99	97	95		98	96	94		96	94	93
5	105	100	96	94		103	99	96	93		97	94	92		96	93	92		94	93	91
6	102	97	94	91		101	96	93	91		95	92	90		94	92	90		93	91	89
7	100	95	91	89		99	94	91	89		93	90	88		92	90	88		91	89	88
8	98	93	89	87		97	92	89	87		91	89	87		91	88	86		90	88	86
9	96	91	88	85		96	91	87	85		90	87	85		89	87	85		89	86	85
10	95	89	86	84		94	89	86	84		88	85	83		88	85	83		87	85	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4701619
5°	3833844
10°	1877587
15°	574691
20°	243364
25°	110087
30°	42918
35°	19809
40°	6154
45°	2326
50°	955
55°	344
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2326 cd/sqm

TEST NUMBER: P1252934

CATALOG NUMBER: P3AS24R159030D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1355.7	54.9
10°-20°	831.9	33.7
20°-30°	223.5	9.1
30°-40°	49.2	2.0
40°-50°	6.9	0.3
50°-60°	1.2	0.0
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2411.1	97.7
0°-40°	2460.3	99.6
0°-60°	2468.4	100.0
0°-90°	2469.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2469.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21441	
5°	17417	###
15°	2532	832
25°	455	223
35°	74	49
45°	8	7
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1252934

CATALOG NUMBER: P3AS24R159030D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	21441.1
1°	21307.2
2°	20877.5
3°	20103.2
4°	18937.6
5°	17417.2
6°	15697.4
7°	13781.9
8°	12021.9
9°	10156.0
10°	8432.4
11°	6726.7
12°	5175.4
13°	3980.8
14°	3151.3
15°	2531.5
17.5°	1569.1
20°	1042.9
22.5°	702.2
25°	455.0
27.5°	269.6
30°	169.5
32.5°	114.2
35°	74.0
37.5°	41.2
40°	21.5
42.5°	12.2
45°	7.5
47.5°	4.7
50°	2.8
52.5°	1.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1252934

CATALOG NUMBER: P3AS24R159030D010 E3D1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)