

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253954

Luminaire Tested: P3AS05R409035DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409035DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 460.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253954
CATALOG NUMBER: P3AS05R409035DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1253954
 CATALOG NUMBER: P3AS05R409035DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103259
5°	101386
10°	95567
15°	86811
20°	76260
25°	65133
30°	53958
35°	41599
40°	29598
45°	19940
50°	10882
55°	7684
60°	7236
65°	6693
70°	5963
75°	5676
80°	4546
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19940 cd/sqm



TEST NUMBER: P1253954
 CATALOG NUMBER: P3AS05R409035DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.0	9.3
10°-20°	106.5	23.2
20°-30°	123.2	26.8
30°-40°	97.0	21.1
40°-50°	49.8	10.8
50°-60°	19.1	4.1
60°-70°	12.6	2.7
70°-80°	6.8	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.6	59.3
0°-40°	369.7	80.4
0°-60°	438.5	95.3
0°-90°	460.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	460.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	471	
5°	461	43
15°	382	107
25°	269	123
35°	155	97
45°	64	50
55°	20	19
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1253954

CATALOG NUMBER: P3AS05R409035DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	470.9
2.5°	468.3
5°	460.6
7.5°	447.2
10°	429.2
12.5°	408.1
15°	382.4
17.5°	355.6
20°	326.8
22.5°	297.5
25°	269.2
27.5°	240.9
30°	213.1
32.5°	184.8
35°	155.4
37.5°	128.1
40°	103.4
42.5°	82.3
45°	64.3
47.5°	46.8
50°	31.9
52.5°	23.2
55°	20.1
57.5°	18.0
60°	16.5
62.5°	14.4
65°	12.9
67.5°	10.8
70°	9.3
72.5°	7.7
75°	6.7
77.5°	5.1
80°	3.6
82.5°	3.1
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)