

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253975

Luminaire Tested: P3AS05R459035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 219.0 lumens
Efficiency: N/A
Efficacy: 30.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253975

CATALOG NUMBER: P3AS05R459035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253975

CATALOG NUMBER: P3AS05R459035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47		
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46444
5°	45609
10°	43152
15°	39365
20°	34816
25°	30219
30°	25953
35°	21630
40°	16116
45°	9861
50°	4571
55°	3555
60°	3421
65°	3165
70°	2885
75°	2796
80°	2526
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9861 cd/sqm

TEST NUMBER: P1253975

CATALOG NUMBER: P3AS05R459035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.4	8.8
10°-20°	48.3	22.0
20°-30°	57.4	26.2
30°-40°	49.8	22.8
40°-50°	25.0	11.4
50°-60°	8.7	4.0
60°-70°	6.1	2.8
70°-80°	3.4	1.5
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	125.0	57.1
0°-40°	174.8	79.8
0°-60°	208.5	95.2
0°-90°	219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	219.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	212	
5°	207	19
15°	173	48
25°	125	57
35°	81	50
45°	32	25
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1253975

CATALOG NUMBER: P3AS05R459035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	211.8
2.5°	210.7
5°	207.2
7.5°	201.7
10°	193.8
12.5°	184.2
15°	173.4
17.5°	161.3
20°	149.2
22.5°	136.8
25°	124.9
27.5°	113.6
30°	102.5
32.5°	91.9
35°	80.8
37.5°	68.9
40°	56.3
42.5°	43.9
45°	31.8
47.5°	20.9
50°	13.4
52.5°	10.3
55°	9.3
57.5°	8.6
60°	7.8
62.5°	7.1
65°	6.1
67.5°	5.3
70°	4.5
72.5°	3.8
75°	3.3
77.5°	2.5
80°	2.0
82.5°	1.5
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)