

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252968

Luminaire Tested: P3AS24R209030D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209030D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 969.0 lumens
Efficiency: N/A
Efficacy: 33.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252968

CATALOG NUMBER: P3AS24R209030D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252968

CATALOG NUMBER: P3AS24R209030D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	745532
5°	677700
10°	500859
15°	309832
20°	176929
25°	101014
30°	56642
35°	30811
40°	16889
45°	9303
50°	5424
55°	3938
60°	3684
65°	3424
70°	3013
75°	3135
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9303 cd/sqm

TEST NUMBER: P1252968

CATALOG NUMBER: P3AS24R209030D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.6	27.5
10°-20°	380.6	39.3
20°-30°	198.7	20.5
30°-40°	76.8	7.9
40°-50°	24.9	2.6
50°-60°	9.8	1.0
60°-70°	6.5	0.7
70°-80°	3.8	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	845.9	87.3
0°-40°	922.7	95.2
0°-60°	957.4	98.8
0°-90°	969.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3400	
5°	3079	267
15°	1365	381
25°	418	199
35°	115	77
45°	30	25
55°	10	10
65°	7	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1252968

CATALOG NUMBER: P3AS24R209030D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3399.9
1°	3393.4
2°	3353.1
3°	3291.3
4°	3195.8
5°	3078.8
6°	2940.3
7°	2786.8
8°	2608.9
9°	2435.7
10°	2249.4
12.5°	1787.9
15°	1364.8
17.5°	1021.3
20°	758.2
22.5°	561.7
25°	417.5
27.5°	308.0
30°	223.7
32.5°	161.9
35°	115.1
37.5°	83.3
40°	59.0
42.5°	42.1
45°	30.0
47.5°	21.5
50°	15.9
52.5°	12.2
55°	10.3
57.5°	9.4
60°	8.4
62.5°	7.5
65°	6.6
67.5°	5.6
70°	4.7
72.5°	4.7
75°	3.7
77.5°	2.8
80°	1.9
82.5°	1.9
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)