

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252987

Luminaire Tested: P3AS24R259030D010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1252987  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R259030D010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2430.9 lumens  
Efficiency: N/A  
Efficacy: 84.4 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252987

CATALOG NUMBER: P3AS24R259030D010 E3CD1MMS

### Luminous Intensity Polar Plot



TEST NUMBER: P1252987

CATALOG NUMBER: P3AS24R259030D010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 115 | 113 | 111 | 110 |  | 113 | 111 | 109 | 108 |  | 107 | 106 | 105 |  | 103 | 103 | 102 |  | 100 | 99  | 99  |
| 2   | 112 | 108 | 105 | 103 |  | 110 | 107 | 104 | 102 |  | 104 | 102 | 100 |  | 101 | 99  | 98  |  | 98  | 97  | 96  |
| 3   | 108 | 104 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 98  | 96  |  | 98  | 96  | 94  |  | 96  | 94  | 93  |
| 4   | 105 | 100 | 97  | 94  |  | 104 | 99  | 96  | 93  |  | 97  | 95  | 92  |  | 96  | 93  | 91  |  | 94  | 92  | 90  |
| 5   | 103 | 97  | 93  | 90  |  | 101 | 96  | 93  | 90  |  | 95  | 92  | 89  |  | 93  | 91  | 89  |  | 92  | 90  | 88  |
| 6   | 100 | 94  | 90  | 87  |  | 99  | 93  | 90  | 87  |  | 92  | 89  | 87  |  | 91  | 88  | 86  |  | 90  | 87  | 86  |
| 7   | 97  | 91  | 88  | 85  |  | 96  | 91  | 87  | 85  |  | 90  | 87  | 84  |  | 89  | 86  | 84  |  | 88  | 85  | 83  |
| 8   | 95  | 89  | 85  | 83  |  | 94  | 89  | 85  | 82  |  | 88  | 84  | 82  |  | 87  | 84  | 82  |  | 86  | 83  | 81  |
| 9   | 93  | 87  | 83  | 80  |  | 92  | 86  | 83  | 80  |  | 86  | 82  | 80  |  | 85  | 82  | 80  |  | 84  | 82  | 80  |
| 10  | 91  | 85  | 81  | 78  |  | 90  | 84  | 81  | 78  |  | 84  | 80  | 78  |  | 83  | 80  | 78  |  | 82  | 80  | 78  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2599090 |
| 5°  | 2410581 |
| 10° | 1869460 |
| 15° | 937395  |
| 20° | 307957  |
| 25° | 122451  |
| 30° | 45931   |
| 35° | 13304   |
| 40° | 6011    |
| 45° | 2357    |
| 50° | 1944    |
| 55° | 1453    |
| 60° | 1667    |
| 65° | 1972    |
| 70° | 1218    |
| 75° | 1610    |
| 80° | 2399    |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 2399 cd/sqm

TEST NUMBER: P1252987

CATALOG NUMBER: P3AS24R259030D010 E3CD1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 963.3  | 39.6      |
| 10°-20°   | 1149.2 | 47.3      |
| 20°-30°   | 259.1  | 10.7      |
| 30°-40°   | 42.0   | 1.7       |
| 40°-50°   | 7.6    | 0.3       |
| 50°-60°   | 4.0    | 0.2       |
| 60°-70°   | 3.5    | 0.1       |
| 70°-80°   | 2.0    | 0.1       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 2371.5 | 97.6      |
| 0°-40°    | 2413.5 | 99.3      |
| 0°-60°    | 2425.1 | 99.8      |
| 0°-90°    | 2430.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2430.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 11853 |      |
| 5°  | 10951 | 963  |
| 15° | 4129  | 1149 |
| 25° | 506   | 259  |
| 35° | 50    | 42   |
| 45° | 8     | 8    |
| 55° | 4     | 4    |
| 65° | 4     | 4    |
| 75° | 2     | 2    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1252987

CATALOG NUMBER: P3AS24R259030D010 E3CD1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 11852.8 |
| 1°    | 11833.7 |
| 2°    | 11738.2 |
| 3°    | 11562.5 |
| 4°    | 11297.0 |
| 5°    | 10951.3 |
| 6°    | 10538.8 |
| 7°    | 10091.9 |
| 8°    | 9580.0  |
| 9°    | 9020.4  |
| 10°   | 8395.9  |
| 11°   | 7675.9  |
| 12°   | 6847.0  |
| 13°   | 5979.9  |
| 14°   | 5049.8  |
| 15°   | 4129.2  |
| 17.5° | 2353.0  |
| 20°   | 1319.7  |
| 22.5° | 796.4   |
| 25°   | 506.1   |
| 27.5° | 311.3   |
| 30°   | 181.4   |
| 32.5° | 95.5    |
| 35°   | 49.7    |
| 37.5° | 32.5    |
| 40°   | 21.0    |
| 42.5° | 13.4    |
| 45°   | 7.6     |
| 47.5° | 5.7     |
| 50°   | 5.7     |
| 52.5° | 5.7     |
| 55°   | 3.8     |
| 57.5° | 3.8     |
| 60°   | 3.8     |
| 62.5° | 3.8     |
| 65°   | 3.8     |
| 67.5° | 3.8     |
| 70°   | 1.9     |
| 72.5° | 1.9     |
| 75°   | 1.9     |
| 77.5° | 1.9     |
| 80°   | 1.9     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |



TEST NUMBER: P1252987

CATALOG NUMBER: P3AS24R259030D010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)