

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253993

Luminaire Tested: P3AS05R509035DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509035DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 716.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253993
CATALOG NUMBER: P3AS05R509035DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1253993
 CATALOG NUMBER: P3AS05R509035DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	14.5
10°-20°	256.8	35.9
20°-30°	269.9	37.7
30°-40°	77.3	10.8
40°-50°	7.5	1.1
50°-60°	0.6	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	630.4	88.0
0°-40°	707.6	98.8
0°-60°	715.8	100.0
0°-90°	716.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	716.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1141	
5°	1106	104
15°	927	257
25°	617	270
35°	100	77
45°	8	8
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1253993
CATALOG NUMBER: P3AS05R509035DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1141.1
1°	1139.3
2°	1134.2
3°	1126.9
4°	1117.1
5°	1106.5
6°	1095.1
7°	1083.0
8°	1071.6
9°	1058.5
10°	1043.8
11°	1026.9
12°	1007.4
13°	983.2
14°	956.9
15°	926.8
16°	895.0
17°	864.2
18°	832.6
19°	804.8
20°	780.1
21°	756.3
22°	729.3
23°	698.2
24°	661.9
25°	617.1
26°	568.6
27°	514.6
28°	460.8
29°	402.7
30°	338.8
31°	278.9
32°	223.8
32.5°	199.8
33°	175.6
34°	134.6
35°	99.5
36°	73.0
37°	54.3
37.5°	47.0
38°	40.7
39°	31.6
40°	25.0
42.5°	14.1
45°	8.1



TEST NUMBER: P1253993
CATALOG NUMBER: P3AS05R509035DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	4.5
50°	1.8
52.5°	0.8
55°	0.5
57.5°	0.5
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)