

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254010

Luminaire Tested: P3AS05R509035DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509035DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 186.0 lumens
Efficiency: N/A
Efficacy: 25.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254010

CATALOG NUMBER: P3AS05R509035DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254010

CATALOG NUMBER: P3AS05R509035DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		76
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54097
5°	52652
10°	48541
15°	42679
20°	35726
25°	28332
30°	20788
35°	14295
40°	9074
45°	5086
50°	2763
55°	2294
60°	1974
65°	1816
70°	1603
75°	1525
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5086 cd/sqm

TEST NUMBER: P1254010

CATALOG NUMBER: P3AS05R509035DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.2	11.9
10°-20°	52.1	28.0
20°-30°	53.3	28.6
30°-40°	33.8	18.2
40°-50°	13.5	7.2
50°-60°	5.4	2.9
60°-70°	3.5	1.9
70°-80°	1.8	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	127.5	68.5
0°-40°	161.3	86.7
0°-60°	180.2	96.9
0°-90°	186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	247	
5°	239	22
15°	188	52
25°	117	53
35°	53	34
45°	16	13
55°	6	5
65°	4	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1254010

CATALOG NUMBER: P3AS05R509035DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	246.7
2.5°	244.9
5°	239.2
7.5°	230.1
10°	218.0
12.5°	203.7
15°	188.0
17.5°	170.9
20°	153.1
22.5°	135.2
25°	117.1
27.5°	98.9
30°	82.1
32.5°	67.0
35°	53.4
37.5°	41.8
40°	31.7
42.5°	23.4
45°	16.4
47.5°	11.1
50°	8.1
52.5°	6.8
55°	6.0
57.5°	5.3
60°	4.5
62.5°	4.0
65°	3.5
67.5°	3.0
70°	2.5
72.5°	2.0
75°	1.8
77.5°	1.3
80°	1.0
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)