

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254033

Luminaire Tested: P3AS05R559035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 214.0 lumens
Efficiency: N/A
Efficacy: 29.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254033

CATALOG NUMBER: P3AS05R559035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254033

CATALOG NUMBER: P3AS05R559035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40238
5°	39731
10°	38165
15°	35687
20°	32553
25°	29058
30°	25396
35°	21121
40°	16631
45°	11288
50°	6891
55°	3594
60°	3333
65°	3165
70°	2885
75°	2542
80°	2526
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11288 cd/sqm

TEST NUMBER: P1254033

CATALOG NUMBER: P3AS05R559035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.9	7.9
10°-20°	43.9	20.5
20°-30°	55.0	25.7
30°-40°	49.1	23.0
40°-50°	28.8	13.4
50°-60°	9.9	4.6
60°-70°	6.0	2.8
70°-80°	3.3	1.5
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.9	54.2
0°-40°	165.0	77.1
0°-60°	203.7	95.2
0°-90°	214.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	214.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	184	
5°	180	17
15°	157	44
25°	120	55
35°	79	49
45°	36	29
55°	9	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1254033

CATALOG NUMBER: P3AS05R559035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	183.5
2.5°	182.5
5°	180.5
7.5°	176.4
10°	171.4
12.5°	165.0
15°	157.2
17.5°	148.9
20°	139.5
22.5°	129.9
25°	120.1
27.5°	110.2
30°	100.3
32.5°	89.7
35°	78.9
37.5°	68.2
40°	58.1
42.5°	47.3
45°	36.4
47.5°	27.8
50°	20.2
52.5°	13.1
55°	9.4
57.5°	8.3
60°	7.6
62.5°	6.8
65°	6.1
67.5°	5.3
70°	4.5
72.5°	3.8
75°	3.0
77.5°	2.5
80°	2.0
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)