

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254043

Luminaire Tested: P3AS05R559035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 562.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254043

CATALOG NUMBER: P3AS05R559035DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1254043

CATALOG NUMBER: P3AS05R559035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154330
5°	152762
10°	147515
15°	136346
20°	117657
25°	92933
30°	65934
35°	42510
40°	25534
45°	14389
50°	7744
55°	2753
60°	2500
65°	2387
70°	2308
75°	2203
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1254043

CATALOG NUMBER: P3AS05R559035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	11.6
10°-20°	166.1	29.6
20°-30°	174.1	31.0
30°-40°	101.5	18.1
40°-50°	38.0	6.8
50°-60°	8.9	1.6
60°-70°	4.6	0.8
70°-80°	2.7	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.4	72.1
0°-40°	507.0	90.2
0°-60°	553.9	98.6
0°-90°	562.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	562.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	704	
5°	694	65
15°	601	166
25°	384	174
35°	159	102
45°	46	38
55°	7	9
65°	5	5
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1254043

CATALOG NUMBER: P3AS05R559035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	703.8
2.5°	701.7
5°	694.0
7.5°	681.6
10°	662.5
12.5°	635.7
15°	600.6
17.5°	556.3
20°	504.2
22.5°	446.0
25°	384.1
27.5°	320.7
30°	260.4
32.5°	205.7
35°	158.8
37.5°	120.6
40°	89.2
42.5°	63.9
45°	46.4
47.5°	33.5
50°	22.7
52.5°	12.9
55°	7.2
57.5°	6.2
60°	5.7
62.5°	5.2
65°	4.6
67.5°	4.1
70°	3.6
72.5°	3.1
75°	2.6
77.5°	2.1
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)