

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254075

Luminaire Tested: P3AS05R659035DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659035DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 637.0 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254075

CATALOG NUMBER: P3AS05R659035DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1254075

CATALOG NUMBER: P3AS05R659035DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155667
5°	146511
10°	144642
15°	142089
20°	134155
25°	124531
30°	96800
35°	56001
40°	22557
45°	10389
50°	4025
55°	1567
60°	1360
65°	1349
70°	1346
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10389 cd/sqm

TEST NUMBER: P1254075

CATALOG NUMBER: P3AS05R659035DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.3	9.9
10°-20°	174.8	27.4
20°-30°	228.8	35.9
30°-40°	132.5	20.8
40°-50°	28.4	4.5
50°-60°	4.6	0.7
60°-70°	2.6	0.4
70°-80°	1.5	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.9	73.3
0°-40°	599.4	94.1
0°-60°	632.4	99.3
0°-90°	637.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	637.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	710	
5°	666	63
15°	626	175
25°	515	229
35°	209	133
45°	34	28
55°	4	5
65°	3	3
75°	2	1
85°	0	1
90°	0	

TEST NUMBER: P1254075

CATALOG NUMBER: P3AS05R659035DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	709.9
2.5°	689.8
5°	665.6
7.5°	655.8
10°	649.6
12.5°	640.9
15°	625.9
17.5°	602.8
20°	574.9
22.5°	548.7
25°	514.7
27.5°	457.5
30°	382.3
32.5°	296.2
35°	209.2
37.5°	132.4
40°	78.8
42.5°	49.5
45°	33.5
47.5°	21.6
50°	11.8
52.5°	5.7
55°	4.1
57.5°	3.6
60°	3.1
62.5°	3.1
65°	2.6
67.5°	2.1
70°	2.1
72.5°	1.5
75°	1.5
77.5°	1.0
80°	1.0
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)