

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254107

Luminaire Tested: P3AS05R709035DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709035DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 644.0 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254107

CATALOG NUMBER: P3AS05R709035DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1254107

CATALOG NUMBER: P3AS05R709035DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127884
5°	122034
10°	116097
15°	112986
20°	108813
25°	102998
30°	95787
35°	80468
40°	51869
45°	24096
50°	6311
55°	1567
60°	1579
65°	1349
70°	1346
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24096 cd/sqm

TEST NUMBER: P1254107

CATALOG NUMBER: P3AS05R709035DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	8.1
10°-20°	139.9	21.7
20°-30°	195.4	30.3
30°-40°	181.2	28.1
40°-50°	64.9	10.1
50°-60°	5.5	0.9
60°-70°	2.8	0.4
70°-80°	1.8	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.2	60.1
0°-40°	568.3	88.3
0°-60°	638.8	99.2
0°-90°	644.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	644.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	583	
5°	554	52
15°	498	140
25°	426	195
35°	301	181
45°	78	65
55°	4	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1254107

CATALOG NUMBER: P3AS05R709035DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	583.2
2.5°	574.4
5°	554.4
7.5°	535.8
10°	521.4
12.5°	509.6
15°	497.7
17.5°	483.3
20°	466.3
22.5°	446.8
25°	425.7
27.5°	404.1
30°	378.3
32.5°	345.4
35°	300.6
37.5°	243.5
40°	181.2
42.5°	123.5
45°	77.7
47.5°	43.2
50°	18.5
52.5°	6.2
55°	4.1
57.5°	3.6
60°	3.6
62.5°	3.1
65°	2.6
67.5°	2.6
70°	2.1
72.5°	2.1
75°	1.5
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)