

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253145

Luminaire Tested: P3AS24R509030D010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1253145  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R509030D010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2148.0 lumens  
Efficiency: N/A  
Efficacy: 74.6 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253145  
CATALOG NUMBER: P3AS24R509030D010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1253145  
 CATALOG NUMBER: P3AS24R509030D010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76				76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67				67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64				64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60				60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57				57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54				54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	683893
5°	670106
10°	627666
15°	561887
20°	472844
25°	360892
30°	234542
35°	139066
40°	80351
45°	40283
50°	14976
55°	11699
60°	10876
65°	9910
70°	9809
75°	9743
80°	9597
85°	9561

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 40283 cd/sqm



TEST NUMBER: P1253145  
 CATALOG NUMBER: P3AS24R509030D010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	283.2	13.2
10°-20°	684.5	31.9
20°-30°	671.5	31.3
30°-40°	338.3	15.8
40°-50°	106.9	5.0
50°-60°	27.7	1.3
60°-70°	19.6	0.9
70°-80°	12.1	0.6
80°-90°	4.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1639.2	76.3
0°-40°	1977.6	92.1
0°-60°	2112.2	98.3
0°-90°	2148.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2148.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3119	
5°	3044	283
15°	2475	684
25°	1492	672
35°	520	338
45°	130	107
55°	31	28
65°	19	20
75°	12	12
85°	4	4
90°	0	

TEST NUMBER: P1253145

CATALOG NUMBER: P3AS24R509030D010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3118.8
2.5°	3099.7
5°	3044.3
7.5°	2945.0
10°	2818.9
12.5°	2656.6
15°	2475.1
17.5°	2265.1
20°	2026.3
22.5°	1768.5
25°	1491.6
27.5°	1197.5
30°	926.3
32.5°	697.1
35°	519.5
37.5°	383.9
40°	280.7
42.5°	198.6
45°	129.9
47.5°	74.5
50°	43.9
52.5°	32.5
55°	30.6
57.5°	26.7
60°	24.8
62.5°	22.9
65°	19.1
67.5°	17.2
70°	15.3
72.5°	13.4
75°	11.5
77.5°	9.5
80°	7.6
82.5°	5.7
85°	3.8
87.5°	1.9
90°	0.0

(END OF REPORT)