

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253159

Luminaire Tested: P3AS24R559030D010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1253159  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R559030D010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2541.0 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253159  
CATALOG NUMBER: P3AS24R559030D010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1253159

CATALOG NUMBER: P3AS24R559030D010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94				94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89				89
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84				84
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79				79
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74				74
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70				70
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66				66
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63				63
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60				60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57				57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	704768
5°	698193
10°	726261
15°	716190
20°	660414
25°	537346
30°	326379
35°	112966
40°	32260
45°	15412
50°	6516
55°	2906
60°	3333
65°	2958
70°	2436
75°	3219
80°	2399
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15412 cd/sqm



TEST NUMBER: P1253159  
 CATALOG NUMBER: P3AS24R559030D010 E3CB1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	306.6	12.1
10°-20°	876.8	34.5
20°-30°	977.5	38.5
30°-40°	319.8	12.6
40°-50°	42.2	1.7
50°-60°	8.9	0.4
60°-70°	5.2	0.2
70°-80°	3.3	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2160.9	85.0
0°-40°	2480.7	97.6
0°-60°	2531.8	99.6
0°-90°	2541.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2541.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3214	
5°	3172	307
15°	3155	877
25°	2221	977
35°	422	320
45°	50	42
55°	8	9
65°	6	5
75°	4	3
85°	0	1
90°	0	



TEST NUMBER: P1253159  
CATALOG NUMBER: P3AS24R559030D010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3214.0
2.5°	3191.0
5°	3171.9
7.5°	3217.8
10°	3261.7
12.5°	3238.8
15°	3154.8
17.5°	3021.1
20°	2830.1
22.5°	2566.6
25°	2220.9
27.5°	1781.7
30°	1289.0
32.5°	790.6
35°	422.0
37.5°	213.9
40°	112.7
42.5°	72.6
45°	49.7
47.5°	34.4
50°	19.1
52.5°	11.5
55°	7.6
57.5°	7.6
60°	7.6
62.5°	5.7
65°	5.7
67.5°	3.8
70°	3.8
72.5°	3.8
75°	3.8
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)