

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254170

Luminaire Tested: P3AS09R159035DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159035DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 383.0 lumens
Efficiency: N/A
Efficacy: 34.5 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254170

CATALOG NUMBER: P3AS09R159035DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254170

CATALOG NUMBER: P3AS09R159035DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	90	89
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	86	85
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	82	81
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	79	78
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	76	75
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	73	72
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	71	70
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	68	67
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	66	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	327189
5°	290424
10°	201689
15°	119274
20°	67929
25°	38833
30°	21497
35°	11457
40°	6326
45°	3442
50°	2149
55°	1682
60°	1447
65°	1349
70°	1154
75°	1271
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3442 cd/sqm

TEST NUMBER: P1254170

CATALOG NUMBER: P3AS09R159035DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.2	29.3
10°-20°	148.1	38.7
20°-30°	76.2	19.9
30°-40°	28.6	7.5
40°-50°	9.4	2.4
50°-60°	4.0	1.1
60°-70°	2.6	0.7
70°-80°	1.5	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.5	87.9
0°-40°	365.1	95.3
0°-60°	378.5	98.8
0°-90°	383.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	383.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1492	
5°	1319	112
15°	525	148
25°	160	76
35°	43	29
45°	11	9
55°	4	4
65°	3	3
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1254170

CATALOG NUMBER: P3AS09R159035DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1492.1
1°	1489.1
2°	1469.6
3°	1432.3
4°	1383.2
5°	1319.4
6°	1247.1
7°	1167.8
8°	1079.6
9°	992.5
10°	905.8
12.5°	697.0
15°	525.4
17.5°	393.3
20°	291.1
22.5°	217.3
25°	160.5
27.5°	117.0
30°	84.9
32.5°	60.1
35°	42.8
37.5°	30.6
40°	22.1
42.5°	15.9
45°	11.1
47.5°	8.1
50°	6.3
52.5°	5.2
55°	4.4
57.5°	3.7
60°	3.3
62.5°	3.0
65°	2.6
67.5°	2.2
70°	1.8
72.5°	1.8
75°	1.5
77.5°	1.1
80°	0.7
82.5°	0.7
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)