

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254176

Luminaire Tested: P3AS09R159035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 291.0 lumens
Efficiency: N/A
Efficacy: 26.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254176

CATALOG NUMBER: P3AS09R159035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1254176

CATALOG NUMBER: P3AS09R159035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73393
5°	71406
10°	65263
15°	57163
20°	49028
25°	40938
30°	32765
35°	24574
40°	17833
45°	11660
50°	7300
55°	4932
60°	4386
65°	3995
70°	3783
75°	3474
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11660 cd/sqm

TEST NUMBER: P1254176

CATALOG NUMBER: P3AS09R159035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.9	10.3
10°-20°	70.2	24.1
20°-30°	77.3	26.6
30°-40°	57.9	19.9
40°-50°	30.0	10.3
50°-60°	12.4	4.3
60°-70°	7.7	2.6
70°-80°	4.3	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.4	61.0
0°-40°	235.3	80.9
0°-60°	277.7	95.4
0°-90°	291.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	291.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	335	
5°	324	30
15°	252	70
25°	169	77
35°	92	58
45°	38	30
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1254176

CATALOG NUMBER: P3AS09R159035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	334.7
1°	335.1
2°	334.0
3°	331.8
4°	328.5
5°	324.4
6°	319.3
7°	313.7
8°	307.1
9°	300.1
10°	293.1
12.5°	272.8
15°	251.8
17.5°	230.8
20°	210.1
22.5°	189.1
25°	169.2
27.5°	149.3
30°	129.4
32.5°	109.9
35°	91.8
37.5°	76.3
40°	62.3
42.5°	49.4
45°	37.6
47.5°	28.4
50°	21.4
52.5°	15.9
55°	12.9
57.5°	11.4
60°	10.0
62.5°	8.8
65°	7.7
67.5°	6.6
70°	5.9
72.5°	4.8
75°	4.1
77.5°	3.3
80°	2.6
82.5°	1.8
85°	1.1
87.5°	0.4
90°	0.0

(END OF REPORT)