

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253198

Luminaire Tested: P3AS24R609030D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R609030D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 985.0 lumens
Efficiency: N/A
Efficacy: 34.2 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253198

CATALOG NUMBER: P3AS24R609030D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253198

CATALOG NUMBER: P3AS24R609030D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	232591
5°	230398
10°	223665
15°	209559
20°	185469
25°	155162
30°	121614
35°	88205
40°	58681
45°	36593
50°	19786
55°	5735
60°	5350
65°	4877
70°	4809
75°	4745
80°	4672
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36593 cd/sqm

TEST NUMBER: P1253198

CATALOG NUMBER: P3AS24R609030D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.6	10.0
10°-20°	256.1	26.0
20°-30°	291.9	29.6
30°-40°	207.0	21.0
40°-50°	93.9	9.5
50°-60°	19.9	2.0
60°-70°	9.6	1.0
70°-80°	5.9	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.6	65.6
0°-40°	853.6	86.7
0°-60°	967.4	98.2
0°-90°	985.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	985.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1061	
5°	1047	99
15°	923	256
25°	641	292
35°	330	207
45°	118	94
55°	15	20
65°	9	10
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1253198

CATALOG NUMBER: P3AS24R609030D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1060.7
2.5°	1057.0
5°	1046.7
7.5°	1028.9
10°	1004.5
12.5°	969.9
15°	923.1
17.5°	864.1
20°	794.8
22.5°	719.9
25°	641.3
27.5°	560.8
30°	480.3
32.5°	403.5
35°	329.5
37.5°	264.0
40°	205.0
42.5°	155.4
45°	118.0
47.5°	88.0
50°	58.0
52.5°	27.1
55°	15.0
57.5°	13.1
60°	12.2
62.5°	11.2
65°	9.4
67.5°	8.4
70°	7.5
72.5°	6.6
75°	5.6
77.5°	4.7
80°	3.7
82.5°	2.8
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)