

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253205

Luminaire Tested: P3AS24R609030D010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1253205  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R609030D010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1574.0 lumens  
Efficiency: N/A  
Efficacy: 54.7 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253205  
CATALOG NUMBER: P3AS24R609030D010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1253205  
 CATALOG NUMBER: P3AS24R609030D010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	279407
5°	276270
10°	266706
15°	251965
20°	232257
25°	210302
30°	186712
35°	159545
40°	126866
45°	89467
50°	53423
55°	27029
60°	25963
65°	23764
70°	22055
75°	21011
80°	19321
85°	14341

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 89467 cd/sqm



TEST NUMBER: P1253205  
 CATALOG NUMBER: P3AS24R609030D010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.9	7.5
10°-20°	310.2	19.7
20°-30°	398.3	25.3
30°-40°	369.3	23.5
40°-50°	224.8	14.3
50°-60°	74.9	4.8
60°-70°	45.6	2.9
70°-80°	25.7	1.6
80°-90°	7.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	826.4	52.5
0°-40°	1195.7	76.0
0°-60°	1495.4	95.0
0°-90°	1574.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1574.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1274	
5°	1255	118
15°	1110	310
25°	869	398
35°	596	369
45°	288	225
55°	71	75
65°	46	46
75°	25	26
85°	6	7
90°	0	

TEST NUMBER: P1253205  
CATALOG NUMBER: P3AS24R609030D010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1274.2
2.5°	1268.5
5°	1255.1
7.5°	1230.3
10°	1197.8
12.5°	1157.7
15°	1109.9
17.5°	1054.5
20°	995.3
22.5°	932.3
25°	869.2
27.5°	804.3
30°	737.4
32.5°	670.5
35°	596.0
37.5°	517.7
40°	443.2
42.5°	364.9
45°	288.5
47.5°	223.5
50°	156.6
52.5°	93.6
55°	70.7
57.5°	65.0
60°	59.2
62.5°	51.6
65°	45.8
67.5°	40.1
70°	34.4
72.5°	28.7
75°	24.8
77.5°	19.1
80°	15.3
82.5°	9.6
85°	5.7
87.5°	3.8
90°	0.0

(END OF REPORT)