

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254195

Luminaire Tested: P3AS09R209035DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209035DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 951.1 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254195
CATALOG NUMBER: P3AS09R209035DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1254195
 CATALOG NUMBER: P3AS09R209035DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98		98
2	112	109	106	104	110	108	105	103	104	103	101	102	100	99	99	98	97	95		95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	93		93
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92	91		91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	90		90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	88		88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	86		86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85		85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83		83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	82		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1477009
5°	1281991
10°	792147
15°	275121
20°	84497
25°	29881
30°	11065
35°	4444
40°	2376
45°	930
50°	512
55°	573
60°	658
65°	415
70°	513
75°	678
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 930 cd/sqm



TEST NUMBER: P1254195
 CATALOG NUMBER: P3AS09R209035DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	483.4	50.8
10°-20°	383.5	40.3
20°-30°	66.4	7.0
30°-40°	12.1	1.3
40°-50°	2.8	0.3
50°-60°	1.3	0.1
60°-70°	0.9	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	933.3	98.1
0°-40°	945.4	99.4
0°-60°	949.5	99.8
0°-90°	951.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	951.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6736	
5°	5824	483
15°	1212	384
25°	124	66
35°	17	12
45°	3	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1254195
CATALOG NUMBER: P3AS09R209035DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6735.7
1°	6703.3
2°	6575.4
3°	6369.9
4°	6129.0
5°	5824.1
6°	5474.8
7°	5068.3
8°	4605.4
9°	4085.2
10°	3557.6
12.5°	2244.0
15°	1211.9
17.5°	647.4
20°	362.1
22.5°	207.0
25°	123.5
27.5°	75.3
30°	43.7
32.5°	25.6
35°	16.6
37.5°	11.3
40°	8.3
42.5°	5.3
45°	3.0
47.5°	1.5
50°	1.5
52.5°	1.5
55°	1.5
57.5°	1.5
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)