

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254203

Luminaire Tested: P3AS09R209035DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254203
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209035DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 779.1 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254203
CATALOG NUMBER: P3AS09R209035DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1254203
 CATALOG NUMBER: P3AS09R209035DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	599360
5°	544815
10°	402665
15°	249082
20°	142252
25°	81198
30°	45551
35°	24788
40°	13568
45°	7474
50°	4367
55°	3173
60°	2982
65°	2750
70°	2436
75°	2542
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7474 cd/sqm



TEST NUMBER: P1254203
 CATALOG NUMBER: P3AS09R209035DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.3	27.5
10°-20°	306.0	39.3
20°-30°	159.7	20.5
30°-40°	61.8	7.9
40°-50°	20.0	2.6
50°-60°	7.9	1.0
60°-70°	5.2	0.7
70°-80°	3.1	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.0	87.3
0°-40°	741.8	95.2
0°-60°	769.7	98.8
0°-90°	779.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	779.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2733	
5°	2475	214
15°	1097	306
25°	336	160
35°	93	62
45°	24	20
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1254203
CATALOG NUMBER: P3AS09R209035DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2733.3
1°	2728.0
2°	2695.6
3°	2646.0
4°	2569.2
5°	2475.1
6°	2363.8
7°	2240.3
8°	2097.4
9°	1958.1
10°	1808.4
12.5°	1437.4
15°	1097.2
17.5°	821.0
20°	609.6
22.5°	451.5
25°	335.6
27.5°	247.6
30°	179.9
32.5°	130.2
35°	92.6
37.5°	67.0
40°	47.4
42.5°	33.9
45°	24.1
47.5°	17.3
50°	12.8
52.5°	9.8
55°	8.3
57.5°	7.5
60°	6.8
62.5°	6.0
65°	5.3
67.5°	4.5
70°	3.8
72.5°	3.8
75°	3.0
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)