

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253336

Luminaire Tested: P3AS02R109035DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109035DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 184.9 lumens
Efficiency: N/A
Efficacy: 48.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253336
CATALOG NUMBER: P3AS02R109035DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1253336
 CATALOG NUMBER: P3AS02R109035DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			
4	94	86	80	75	92	85	79	74	82	77	74	80	76	73	78	75	72	70			
5	89	80	73	68	87	79	73	68	77	72	68	75	71	67	74	70	66	65			
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			
7	80	70	63	58	78	69	63	58	67	62	58	66	61	58	65	61	57	56			
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46663
5°	45388
10°	41482
15°	36345
20°	31176
25°	26034
30°	20839
35°	15633
40°	11336
45°	7412
50°	4640
55°	3135
60°	2763
65°	2542
70°	2372
75°	2203
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7412 cd/sqm



TEST NUMBER: P1253336
 CATALOG NUMBER: P3AS02R109035DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.0	10.3
10°-20°	44.6	24.1
20°-30°	49.1	26.6
30°-40°	36.8	19.9
40°-50°	19.1	10.3
50°-60°	7.9	4.3
60°-70°	4.9	2.6
70°-80°	2.7	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	112.8	61.0
0°-40°	149.6	80.9
0°-60°	176.6	95.5
0°-90°	184.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	184.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	213	
5°	206	19
15°	160	45
25°	108	49
35°	58	37
45°	24	19
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1253336
CATALOG NUMBER: P3AS02R109035DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	212.8
1°	213.0
2°	212.3
3°	210.9
4°	208.8
5°	206.2
6°	203.0
7°	199.4
8°	195.2
9°	190.8
10°	186.3
12.5°	173.4
15°	160.1
17.5°	146.7
20°	133.6
22.5°	120.2
25°	107.6
27.5°	94.9
30°	82.3
32.5°	69.8
35°	58.4
37.5°	48.5
40°	39.6
42.5°	31.4
45°	23.9
47.5°	18.0
50°	13.6
52.5°	10.1
55°	8.2
57.5°	7.3
60°	6.3
62.5°	5.6
65°	4.9
67.5°	4.2
70°	3.7
72.5°	3.0
75°	2.6
77.5°	2.1
80°	1.6
82.5°	1.2
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)