

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253368

Luminaire Tested: P3AS02R129035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 196.9 lumens
Efficiency: N/A
Efficacy: 53.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253368

CATALOG NUMBER: P3AS02R129035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253368

CATALOG NUMBER: P3AS02R129035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	74		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	83	74	67	63	72	66	62		70	66	62		69
7	80	70	63	58	78	69	63	58	67	62	58		66	61	58		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49689
5°	48338
10°	44176
15°	38706
20°	33206
25°	27727
30°	22181
35°	16624
40°	12080
45°	7908
50°	4947
55°	3326
60°	2938
65°	2698
70°	2565
75°	2288
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7908 cd/sqm

TEST NUMBER: P1253368

CATALOG NUMBER: P3AS02R129035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.3	10.3
10°-20°	47.5	24.1
20°-30°	52.3	26.6
30°-40°	39.2	19.9
40°-50°	20.3	10.3
50°-60°	8.4	4.3
60°-70°	5.2	2.6
70°-80°	2.9	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	120.1	61.0
0°-40°	159.3	80.9
0°-60°	188.0	95.5
0°-90°	196.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	196.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	227	
5°	220	20
15°	170	47
25°	115	52
35°	62	39
45°	26	20
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1253368

CATALOG NUMBER: P3AS02R129035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	226.6
1°	226.9
2°	226.1
3°	224.6
4°	222.4
5°	219.6
6°	216.1
7°	212.4
8°	207.9
9°	203.1
10°	198.4
12.5°	184.7
15°	170.5
17.5°	156.2
20°	142.3
22.5°	128.0
25°	114.6
27.5°	101.1
30°	87.6
32.5°	74.4
35°	62.1
37.5°	51.7
40°	42.2
42.5°	33.4
45°	25.5
47.5°	19.2
50°	14.5
52.5°	10.7
55°	8.7
57.5°	7.7
60°	6.7
62.5°	6.0
65°	5.2
67.5°	4.5
70°	4.0
72.5°	3.2
75°	2.7
77.5°	2.2
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)