

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253374

Luminaire Tested: P3AS02R129035DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253374
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129035DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 192.0 lumens
Efficiency: N/A
Efficacy: 51.9 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253374
CATALOG NUMBER: P3AS02R129035DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1253374
 CATALOG NUMBER: P3AS02R129035DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80	80	80	80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72	72	72	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66	66	66	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60	60	60	60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55	55	55	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51	51	51	51
8	72	62	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55873
5°	52388
10°	42952
15°	33371
20°	26346
25°	21001
30°	16838
35°	13759
40°	11336
45°	9520
50°	8187
55°	7073
60°	6271
65°	5448
70°	4873
75°	3897
80°	3157
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9520 cd/sqm



TEST NUMBER: P1253374

CATALOG NUMBER: P3AS02R129035DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.3	11.1
10°-20°	41.2	21.4
20°-30°	40.0	20.8
30°-40°	32.3	16.8
40°-50°	24.0	12.5
50°-60°	16.8	8.7
60°-70°	10.5	5.5
70°-80°	5.0	2.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	102.5	53.4
0°-40°	134.8	70.2
0°-60°	175.6	91.5
0°-90°	192.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	192.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	255	
5°	238	21
15°	147	41
25°	87	40
35°	51	32
45°	31	24
55°	18	17
65°	10	10
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1253374
CATALOG NUMBER: P3AS02R129035DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	254.8
2.5°	250.6
5°	238.0
7.5°	217.7
10°	192.9
12.5°	168.5
15°	147.0
17.5°	128.9
20°	112.9
22.5°	99.0
25°	86.8
27.5°	75.8
30°	66.5
32.5°	58.5
35°	51.4
37.5°	45.1
40°	39.6
42.5°	35.0
45°	30.7
47.5°	27.4
50°	24.0
52.5°	21.1
55°	18.5
57.5°	16.4
60°	14.3
62.5°	12.2
65°	10.5
67.5°	8.8
70°	7.6
72.5°	5.9
75°	4.6
77.5°	3.4
80°	2.5
82.5°	1.3
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)