

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254299

Luminaire Tested: P3AS09R359035DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1254299  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R359035DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 609.1 lumens  
Efficiency: N/A  
Efficacy: 54.9 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1254299  
CATALOG NUMBER: P3AS09R359035DE010 E3DLD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1254299

CATALOG NUMBER: P3AS09R359035DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	139112
5°	136165
10°	127519
15°	114461
20°	99572
25°	84852
30°	71074
35°	56617
40°	40934
45°	25894
50°	14123
55°	9787
60°	9254
65°	8613
70°	8207
75°	7032
80°	6693
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25894 cd/sqm



TEST NUMBER: P1254299

CATALOG NUMBER: P3AS09R359035DE010 E3DLD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.6	9.5
10°-20°	140.3	23.0
20°-30°	160.8	26.4
30°-40°	131.2	21.5
40°-50°	66.2	10.9
50°-60°	24.6	4.0
60°-70°	16.5	2.7
70°-80°	9.1	1.5
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.7	58.9
0°-40°	489.9	80.4
0°-60°	580.6	95.3
0°-90°	609.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	609.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	634	
5°	619	58
15°	504	140
25°	351	161
35°	212	131
45°	84	66
55°	26	25
65°	17	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1254299

CATALOG NUMBER: P3AS09R359035DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	634.4
1°	633.7
2°	632.2
3°	629.1
4°	624.6
5°	618.6
6°	611.1
7°	603.6
8°	593.8
9°	584.0
10°	572.7
11°	560.7
12°	547.9
13°	533.6
14°	518.5
15°	504.2
17.5°	465.8
20°	426.7
22.5°	386.8
25°	350.7
27.5°	315.3
30°	280.7
32.5°	246.1
35°	211.5
37.5°	176.9
40°	143.0
42.5°	111.4
45°	83.5
47.5°	60.2
50°	41.4
52.5°	30.1
55°	25.6
57.5°	23.3
60°	21.1
62.5°	18.8
65°	16.6
67.5°	14.3
70°	12.8
72.5°	10.5
75°	8.3
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5



TEST NUMBER: P1254299  
CATALOG NUMBER: P3AS09R359035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)