

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253423

Luminaire Tested: P3AS02R209035DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1253423  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R209035DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 259.2 lumens  
Efficiency: N/A  
Efficacy: 72.0 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253423  
CATALOG NUMBER: P3AS02R209035DE010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1253423  
 CATALOG NUMBER: P3AS02R209035DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	74	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	199260
5°	181135
10°	133865
15°	82815
20°	47301
25°	27002
30°	15142
35°	8245
40°	4523
45°	2481
50°	1467
55°	1070
60°	1009
65°	934
70°	833
75°	847
80°	631
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2481 cd/sqm



TEST NUMBER: P1253423  
 CATALOG NUMBER: P3AS02R209035DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.3	27.5
10°-20°	101.7	39.3
20°-30°	53.1	20.5
30°-40°	20.5	7.9
40°-50°	6.7	2.6
50°-60°	2.7	1.0
60°-70°	1.8	0.7
70°-80°	1.1	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	226.1	87.2
0°-40°	246.6	95.2
0°-60°	256.0	98.8
0°-90°	259.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	909	
5°	823	71
15°	365	102
25°	112	53
35°	31	21
45°	8	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1253423  
CATALOG NUMBER: P3AS02R209035DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	908.7
1°	907.0
2°	896.2
3°	879.7
4°	854.2
5°	822.9
6°	785.9
7°	744.9
8°	697.3
9°	651.0
10°	601.2
12.5°	477.9
15°	364.8
17.5°	273.0
20°	202.7
22.5°	150.1
25°	111.6
27.5°	82.3
30°	59.8
32.5°	43.3
35°	30.8
37.5°	22.3
40°	15.8
42.5°	11.3
45°	8.0
47.5°	5.8
50°	4.3
52.5°	3.3
55°	2.8
57.5°	2.5
60°	2.3
62.5°	2.0
65°	1.8
67.5°	1.5
70°	1.3
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)