

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254358

Luminaire Tested: P3AS09R459035DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459035DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 543.0 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254358
CATALOG NUMBER: P3AS09R459035DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1254358
 CATALOG NUMBER: P3AS09R459035DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161741
5°	158045
10°	145800
15°	126788
20°	104146
25°	81029
30°	59832
35°	42108
40°	26278
45°	14234
50°	7710
55°	6614
60°	5921
65°	5085
70°	4360
75°	4490
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14234 cd/sqm



TEST NUMBER: P1254358
 CATALOG NUMBER: P3AS09R459035DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	12.2
10°-20°	154.4	28.4
20°-30°	153.3	28.2
30°-40°	98.7	18.2
40°-50°	38.0	7.0
50°-60°	15.5	2.8
60°-70°	9.8	1.8
70°-80°	5.3	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.1	68.9
0°-40°	472.8	87.1
0°-60°	526.3	96.9
0°-90°	543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	543.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	738	
5°	718	66
15°	558	154
25°	335	153
35°	157	99
45°	46	38
55°	17	15
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1254358
CATALOG NUMBER: P3AS09R459035DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	737.6
2.5°	733.8
5°	718.0
7.5°	690.9
10°	654.8
12.5°	609.6
15°	558.5
17.5°	502.8
20°	446.3
22.5°	389.1
25°	334.9
27.5°	283.7
30°	236.3
32.5°	194.9
35°	157.3
37.5°	123.4
40°	91.8
42.5°	66.2
45°	45.9
47.5°	30.9
50°	22.6
52.5°	18.8
55°	17.3
57.5°	15.1
60°	13.5
62.5°	11.3
65°	9.8
67.5°	8.3
70°	6.8
72.5°	6.0
75°	5.3
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)