

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253429

Luminaire Tested: P3AS02R209035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253429
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 197.1 lumens
Efficiency: N/A
Efficacy: 54.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253429

CATALOG NUMBER: P3AS02R209035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253429

CATALOG NUMBER: P3AS02R209035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		91
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		83
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		76
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		70
5	89	80	73	68	87	79	72	68	77	71	67		75	70	67		64
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		60
7	79	69	63	58	78	69	62	58	67	62	58		66	61	57		55
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		52
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		48
10	68	58	51	47	67	57	51	47	56	51	47		56	50	47		45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48724
5°	47435
10°	43620
15°	38411
20°	32926
25°	27679
30°	22358
35°	17025
40°	12108
45°	8001
50°	4947
55°	3250
60°	2982
65°	2750
70°	2565
75°	2372
80°	2273
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8001 cd/sqm

TEST NUMBER: P1253429

CATALOG NUMBER: P3AS02R209035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.9	10.1
10°-20°	47.1	23.9
20°-30°	52.3	26.5
30°-40°	39.9	20.2
40°-50°	20.4	10.4
50°-60°	8.4	4.3
60°-70°	5.2	2.7
70°-80°	3.0	1.5
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	119.3	60.5
0°-40°	159.2	80.7
0°-60°	188.0	95.4
0°-90°	197.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	197.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	222	
5°	216	20
15°	169	47
25°	114	52
35°	64	40
45°	26	20
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1253429

CATALOG NUMBER: P3AS02R209035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	222.2
1°	222.5
2°	221.5
3°	220.2
4°	218.2
5°	215.5
6°	212.2
7°	208.7
8°	205.0
9°	200.4
10°	195.9
12.5°	182.9
15°	169.2
17.5°	155.2
20°	141.1
22.5°	127.1
25°	114.4
27.5°	101.6
30°	88.3
32.5°	75.8
35°	63.6
37.5°	52.8
40°	42.3
42.5°	33.3
45°	25.8
47.5°	19.5
50°	14.5
52.5°	10.8
55°	8.5
57.5°	7.8
60°	6.8
62.5°	6.0
65°	5.3
67.5°	4.5
70°	4.0
72.5°	3.3
75°	2.8
77.5°	2.3
80°	1.8
82.5°	1.3
85°	0.8
87.5°	0.3
90°	0.0

(END OF REPORT)