

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254390

Luminaire Tested: P3AS09R509035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 847.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254390

CATALOG NUMBER: P3AS09R509035DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1254390

CATALOG NUMBER: P3AS09R509035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269671
5°	264230
10°	247513
15°	221568
20°	186450
25°	142315
30°	92470
35°	54823
40°	31688
45°	15878
50°	5902
55°	4588
60°	4298
65°	3891
70°	3847
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15878 cd/sqm

TEST NUMBER: P1254390

CATALOG NUMBER: P3AS09R509035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	13.2
10°-20°	269.9	31.9
20°-30°	264.8	31.3
30°-40°	133.4	15.7
40°-50°	42.1	5.0
50°-60°	10.9	1.3
60°-70°	7.7	0.9
70°-80°	4.8	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.4	76.3
0°-40°	779.8	92.1
0°-60°	832.8	98.3
0°-90°	847.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	847.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1230	
5°	1200	112
15°	976	270
25°	588	265
35°	205	133
45°	51	42
55°	12	11
65°	8	8
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1254390

CATALOG NUMBER: P3AS09R509035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1229.8
2.5°	1222.3
5°	1200.4
7.5°	1161.3
10°	1111.6
12.5°	1047.5
15°	976.0
17.5°	893.2
20°	799.0
22.5°	697.4
25°	588.2
27.5°	472.2
30°	365.2
32.5°	274.9
35°	204.8
37.5°	151.4
40°	110.7
42.5°	78.3
45°	51.2
47.5°	29.4
50°	17.3
52.5°	12.8
55°	12.0
57.5°	10.5
60°	9.8
62.5°	9.0
65°	7.5
67.5°	6.8
70°	6.0
72.5°	5.3
75°	4.5
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)