

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254488

Luminaire Tested: P3AS09R709035DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709035DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 898.0 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254488

CATALOG NUMBER: P3AS09R709035DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1254488

CATALOG NUMBER: P3AS09R709035DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79		
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174613
5°	164648
10°	156109
15°	153304
20°	147783
25°	139290
30°	138300
35°	120462
40°	77917
45°	36841
50°	5151
55°	421
60°	307
65°	363
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36841 cd/sqm

TEST NUMBER: P1254488

CATALOG NUMBER: P3AS09R709035DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.8	7.8
10°-20°	189.6	21.1
20°-30°	268.3	29.9
30°-40°	269.6	30.0
40°-50°	97.0	10.8
50°-60°	2.6	0.3
60°-70°	0.6	0.1
70°-80°	0.4	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.8	58.8
0°-40°	797.4	88.8
0°-60°	897.0	99.9
0°-90°	898.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	898.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	796	
5°	748	70
15°	675	190
25°	576	268
35°	450	270
45°	119	97
55°	1	3
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1254488

CATALOG NUMBER: P3AS09R709035DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	796.3
1°	794.1
2°	787.1
3°	776.0
4°	762.0
5°	748.0
6°	734.7
7°	724.4
8°	715.1
9°	707.8
10°	701.1
11°	695.6
12°	690.4
13°	685.3
14°	680.5
15°	675.3
16°	669.0
17°	662.4
18°	654.3
19°	644.3
20°	633.3
21°	621.1
22°	608.9
23°	597.1
24°	585.7
25°	575.7
26°	568.7
27°	563.2
28°	558.8
29°	553.6
30°	546.2
31°	535.5
32°	520.4
32.5°	511.9
33°	500.5
34°	478.0
35°	450.0
36°	419.0
37°	383.9
37.5°	367.7
38°	345.6
39°	306.1
40°	272.2
42.5°	188.5
45°	118.8



TEST NUMBER: P1254488

CATALOG NUMBER: P3AS09R709035DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	63.8
50°	15.1
52.5°	1.8
55°	1.1
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)