

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254492

Luminaire Tested: P3AS09R709035DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254492
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709035DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 758.0 lumens
Efficiency: N/A
Efficacy: 68.3 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254492
CATALOG NUMBER: P3AS09R709035DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1254492
 CATALOG NUMBER: P3AS09R709035DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146743
5°	144992
10°	140790
15°	134825
20°	126291
25°	114732
30°	99104
35°	78996
40°	57536
45°	37802
50°	17705
55°	5467
60°	5263
65°	5085
70°	4809
75°	5083
80°	4799
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37802 cd/sqm



TEST NUMBER: P1254492
 CATALOG NUMBER: P3AS09R709035DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	8.2
10°-20°	166.2	21.9
20°-30°	216.0	28.5
30°-40°	183.3	24.2
40°-50°	94.5	12.5
50°-60°	18.2	2.4
60°-70°	9.9	1.3
70°-80°	6.1	0.8
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	444.3	58.6
0°-40°	627.6	82.8
0°-60°	740.3	97.7
0°-90°	758.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	758.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	669	
5°	659	62
15°	594	166
25°	474	216
35°	295	183
45°	122	95
55°	14	18
65°	10	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1254492
CATALOG NUMBER: P3AS09R709035DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	669.2
2.5°	666.9
5°	658.7
7.5°	646.6
10°	632.3
12.5°	614.2
15°	593.9
17.5°	569.1
20°	541.2
22.5°	509.6
25°	474.2
27.5°	434.3
30°	391.4
32.5°	344.0
35°	295.1
37.5°	246.9
40°	201.0
42.5°	158.1
45°	121.9
47.5°	89.6
50°	51.9
52.5°	22.6
55°	14.3
57.5°	13.5
60°	12.0
62.5°	11.3
65°	9.8
67.5°	9.0
70°	7.5
72.5°	6.8
75°	6.0
77.5°	4.5
80°	3.8
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)