

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254497

Luminaire Tested: P3AS09R709035DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1254497  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R709035DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 541.0 lumens  
Efficiency: N/A  
Efficacy: 48.7 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1254497  
CATALOG NUMBER: P3AS09R709035DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1254497  
 CATALOG NUMBER: P3AS09R709035DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126898
5°	124565
10°	117455
15°	106607
20°	93248
25°	78658
30°	64415
35°	49951
40°	35753
45°	22638
50°	11292
55°	6920
60°	5921
65°	5448
70°	4809
75°	4490
80°	3788
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22638 cd/sqm



TEST NUMBER: P1254497  
 CATALOG NUMBER: P3AS09R709035DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.8	9.8
10°-20°	130.7	24.2
20°-30°	148.8	27.5
30°-40°	116.4	21.5
40°-50°	57.2	10.6
50°-60°	17.6	3.2
60°-70°	10.4	1.9
70°-80°	5.6	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.3	61.4
0°-40°	448.6	82.9
0°-60°	523.4	96.7
0°-90°	541.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	541.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	579	
5°	566	53
15°	470	131
25°	325	149
35°	187	116
45°	73	57
55°	18	18
65°	10	10
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1254497  
CATALOG NUMBER: P3AS09R709035DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	578.7
2.5°	575.7
5°	565.9
7.5°	550.1
10°	527.5
12.5°	501.2
15°	469.6
17.5°	435.7
20°	399.6
22.5°	362.0
25°	325.1
27.5°	289.0
30°	254.4
32.5°	219.7
35°	186.6
37.5°	155.0
40°	124.9
42.5°	97.1
45°	73.0
47.5°	51.2
50°	33.1
52.5°	21.8
55°	18.1
57.5°	15.8
60°	13.5
62.5°	12.0
65°	10.5
67.5°	9.0
70°	7.5
72.5°	6.0
75°	5.3
77.5°	4.5
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)