

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253553

Luminaire Tested: P3AS02R409035DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409035DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 292.1 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253553

CATALOG NUMBER: P3AS02R409035DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1253553

CATALOG NUMBER: P3AS02R409035DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	87	83	79	86	82	78		84	81	78		83
6	92	84	79	75	90	83	78	75	82	77	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129200
5°	125445
10°	113848
15°	94053
20°	67836
25°	41954
30°	22712
35°	11752
40°	6383
45°	3566
50°	1808
55°	1338
60°	1228
65°	1193
70°	1154
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3566 cd/sqm

TEST NUMBER: P1253553

CATALOG NUMBER: P3AS02R409035DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	18.0
10°-20°	112.8	38.6
20°-30°	80.5	27.6
30°-40°	29.6	10.1
40°-50°	9.3	3.2
50°-60°	3.3	1.1
60°-70°	2.3	0.8
70°-80°	1.3	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.8	84.2
0°-40°	275.5	94.3
0°-60°	288.1	98.6
0°-90°	292.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	292.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	589	
5°	570	53
15°	414	113
25°	173	80
35°	44	30
45°	12	9
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1253553

CATALOG NUMBER: P3AS02R409035DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	589.2
2.5°	584.7
5°	569.9
7.5°	545.4
10°	511.3
12.5°	467.9
15°	414.3
17.5°	354.1
20°	290.7
22.5°	228.3
25°	173.4
27.5°	127.3
30°	89.7
32.5°	62.9
35°	43.9
37.5°	31.1
40°	22.3
42.5°	16.0
45°	11.5
47.5°	7.8
50°	5.3
52.5°	3.8
55°	3.5
57.5°	3.3
60°	2.8
62.5°	2.5
65°	2.3
67.5°	2.0
70°	1.8
72.5°	1.5
75°	1.3
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)