

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253565

Luminaire Tested: P3AS02R459035DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459035DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 280.1 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253565
CATALOG NUMBER: P3AS02R459035DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1253565
 CATALOG NUMBER: P3AS02R459035DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88	88	88	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83	83	83	83
4	99	92	87	83	97	91	86	82	89	84	81	87	83	80	85	82	79	78	78	78	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74	74	74	74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	69	69	69	69
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66	66	66	66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62	62	62	62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59	59	59	59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105145
5°	102685
10°	94387
15°	79978
20°	62049
25°	43382
30°	27321
35°	16088
40°	9103
45°	4435
50°	1535
55°	1262
60°	1228
65°	1193
70°	1154
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4435 cd/sqm



TEST NUMBER: P1253565
 CATALOG NUMBER: P3AS02R459035DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.2	15.4
10°-20°	96.7	34.5
20°-30°	82.1	29.3
30°-40°	39.2	14.0
40°-50°	11.8	4.2
50°-60°	3.0	1.1
60°-70°	2.3	0.8
70°-80°	1.3	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.1	79.3
0°-40°	261.3	93.3
0°-60°	276.1	98.6
0°-90°	280.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	280.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	480	
5°	466	43
15°	352	97
25°	179	82
35°	60	39
45°	14	12
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1253565
CATALOG NUMBER: P3AS02R459035DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	479.5
2.5°	476.5
5°	466.5
7.5°	449.2
10°	423.9
12.5°	390.4
15°	352.3
17.5°	310.0
20°	265.9
22.5°	221.1
25°	179.3
27.5°	141.2
30°	107.9
32.5°	81.1
35°	60.1
37.5°	44.3
40°	31.8
42.5°	22.0
45°	14.3
47.5°	8.0
50°	4.5
52.5°	3.5
55°	3.3
57.5°	3.0
60°	2.8
62.5°	2.5
65°	2.3
67.5°	2.0
70°	1.8
72.5°	1.5
75°	1.3
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)