

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253568

Luminaire Tested: P3AS02R459035DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459035DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 107.0 lumens
Efficiency: N/A
Efficacy: 29.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253568

CATALOG NUMBER: P3AS02R459035DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253568

CATALOG NUMBER: P3AS02R459035DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		83
3	99	92	86	82	97	91	85	81	88	83	80		85	81	78		75
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		69
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		63
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		58
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		54
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		50
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		47
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22696
5°	22276
10°	21086
15°	19228
20°	17011
25°	14759
30°	12685
35°	10574
40°	7872
45°	4807
50°	2217
55°	1759
60°	1667
65°	1557
70°	1410
75°	1356
80°	1263
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4807 cd/sqm

TEST NUMBER: P1253568

CATALOG NUMBER: P3AS02R459035DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.5	8.8
10°-20°	23.6	22.0
20°-30°	28.0	26.2
30°-40°	24.4	22.8
40°-50°	12.2	11.4
50°-60°	4.3	4.0
60°-70°	3.0	2.8
70°-80°	1.6	1.5
80°-90°	0.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	61.1	57.1
0°-40°	85.4	79.8
0°-60°	101.9	95.2
0°-90°	107.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	107.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	104	
5°	101	9
15°	85	24
25°	61	28
35°	40	24
45°	16	12
55°	5	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1253568

CATALOG NUMBER: P3AS02R459035DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	103.5
2.5°	103.0
5°	101.2
7.5°	98.5
10°	94.7
12.5°	90.0
15°	84.7
17.5°	78.8
20°	72.9
22.5°	66.8
25°	61.0
27.5°	55.5
30°	50.1
32.5°	44.9
35°	39.5
37.5°	33.7
40°	27.5
42.5°	21.5
45°	15.5
47.5°	10.2
50°	6.5
52.5°	5.1
55°	4.6
57.5°	4.2
60°	3.8
62.5°	3.5
65°	3.0
67.5°	2.6
70°	2.2
72.5°	1.8
75°	1.6
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)