

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253581

Luminaire Tested: P3AS02R509035DE010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1253581  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R509035DE010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 343.1 lumens  
Efficiency: N/A  
Efficacy: 95.3 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253581  
CATALOG NUMBER: P3AS02R509035DE010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1253581  
 CATALOG NUMBER: P3AS02R509035DE010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	80	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	72	70	69	69	69	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65	65	65	65
9	81	73	67	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59	59	59	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	119464
5°	117323
10°	112645
15°	103292
20°	91078
25°	69827
30°	37955
35°	12207
40°	2863
45°	403
50°	341
55°	382
60°	351
65°	415
70°	321
75°	424
80°	379
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 85°  
 Luminance: 755 cd/sqm



TEST NUMBER: P1253581  
 CATALOG NUMBER: P3AS02R509035DE010 E3CB1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.0	14.6
10°-20°	126.5	36.9
20°-30°	126.7	36.9
30°-40°	35.6	10.4
40°-50°	2.2	0.6
50°-60°	0.8	0.2
60°-70°	0.7	0.2
70°-80°	0.4	0.1
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	303.2	88.4
0°-40°	338.8	98.7
0°-60°	341.8	99.6
0°-90°	343.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	343.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	545	
5°	533	50
15°	455	126
25°	289	127
35°	46	36
45°	1	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1253581  
CATALOG NUMBER: P3AS02R509035DE010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	544.8
2.5°	542.0
5°	533.0
7.5°	520.7
10°	505.9
12.5°	483.6
15°	455.0
17.5°	422.2
20°	390.3
22.5°	350.7
25°	288.6
27.5°	214.8
30°	149.9
32.5°	90.5
35°	45.6
37.5°	21.6
40°	10.0
42.5°	3.8
45°	1.3
47.5°	1.0
50°	1.0
52.5°	1.0
55°	1.0
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)