

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254560

Luminaire Tested: P3AS13R129035DE010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1254560  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R129035DE010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 90CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 560.0 lumens  
Efficiency: N/A  
Efficacy: 36.1 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1254560  
CATALOG NUMBER: P3AS13R129035DE010 E3DLP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1254560  
 CATALOG NUMBER: P3AS13R129035DE010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	241494
5°	223200
10°	178198
15°	134598
20°	102489
25°	78101
30°	55958
35°	36513
40°	22385
45°	13552
50°	9006
55°	6958
60°	5964
65°	5189
70°	4680
75°	4660
80°	3410
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13552 cd/sqm



TEST NUMBER: P1254560  
 CATALOG NUMBER: P3AS13R129035DE010 E3DLP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.8	16.0
10°-20°	165.7	29.6
20°-30°	147.5	26.3
30°-40°	87.3	15.6
40°-50°	35.8	6.4
50°-60°	16.8	3.0
60°-70°	10.2	1.8
70°-80°	5.4	1.0
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.1	72.0
0°-40°	490.4	87.6
0°-60°	543.0	97.0
0°-90°	560.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	560.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1101	
5°	1014	90
15°	593	166
25°	323	148
35°	136	87
45°	44	36
55°	18	17
65°	10	10
75°	6	5
85°	1	1
90°	0	



TEST NUMBER: P1254560  
CATALOG NUMBER: P3AS13R129035DE010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1101.3
1°	1098.5
2°	1090.3
3°	1074.0
4°	1046.7
5°	1014.0
6°	978.5
7°	936.7
8°	893.0
9°	848.5
10°	800.3
12.5°	690.2
15°	592.9
17.5°	509.3
20°	439.2
22.5°	377.4
25°	322.8
27.5°	270.1
30°	221.0
32.5°	176.4
35°	136.4
37.5°	104.6
40°	78.2
42.5°	58.2
45°	43.7
47.5°	33.6
50°	26.4
52.5°	21.8
55°	18.2
57.5°	15.5
60°	13.6
62.5°	11.8
65°	10.0
67.5°	9.1
70°	7.3
72.5°	6.4
75°	5.5
77.5°	3.6
80°	2.7
82.5°	1.8
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)