

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253602

Luminaire Tested: P3AS02R509035DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509035DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 219.9 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253602

CATALOG NUMBER: P3AS02R509035DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1253602

CATALOG NUMBER: P3AS02R509035DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44711
5°	44046
10°	42106
15°	38979
20°	35050
25°	30800
30°	26181
35°	21228
40°	15944
45°	10265
50°	4878
55°	3823
60°	3640
65°	3373
70°	3077
75°	2796
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10265 cd/sqm

TEST NUMBER: P1253602

CATALOG NUMBER: P3AS02R509035DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.8	8.5
10°-20°	47.9	21.8
20°-30°	58.2	26.5
30°-40°	49.3	22.4
40°-50°	25.6	11.6
50°-60°	9.2	4.2
60°-70°	6.4	2.9
70°-80°	3.5	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	124.8	56.8
0°-40°	174.1	79.2
0°-60°	209.0	95.0
0°-90°	219.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	219.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	204	
5°	200	19
15°	172	48
25°	127	58
35°	79	49
45°	33	26
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1253602

CATALOG NUMBER: P3AS02R509035DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	203.9
2.5°	203.1
5°	200.1
7.5°	195.6
10°	189.1
12.5°	180.8
15°	171.7
17.5°	161.5
20°	150.2
22.5°	138.6
25°	127.3
27.5°	115.5
30°	103.4
32.5°	91.4
35°	79.3
37.5°	67.5
40°	55.7
42.5°	44.4
45°	33.1
47.5°	22.1
50°	14.3
52.5°	11.0
55°	10.0
57.5°	9.0
60°	8.3
62.5°	7.3
65°	6.5
67.5°	5.5
70°	4.8
72.5°	4.0
75°	3.3
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)