

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253616

Luminaire Tested: P3AS02R559035DE010 E3D1LI

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1253616  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R559035DE010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 323.0 lumens  
Efficiency: N/A  
Efficacy: 89.7 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1253616

CATALOG NUMBER: P3AS02R559035DE010 E3D1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1253616

CATALOG NUMBER: P3AS02R559035DE010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  |
| 3   | 104 | 98  | 94  | 90  | 102 | 97  | 93  | 90  | 95  | 91  | 88  |  | 92  | 89  | 87  |  | 90  |
| 4   | 100 | 93  | 88  | 84  | 98  | 92  | 87  | 84  | 90  | 86  | 83  |  | 88  | 84  | 82  |  | 86  |
| 5   | 95  | 88  | 83  | 79  | 94  | 87  | 82  | 78  | 85  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 6   | 91  | 83  | 78  | 74  | 90  | 82  | 77  | 74  | 81  | 76  | 73  |  | 80  | 76  | 73  |  | 78  |
| 7   | 87  | 79  | 73  | 70  | 86  | 78  | 73  | 69  | 77  | 72  | 69  |  | 76  | 72  | 69  |  | 75  |
| 8   | 83  | 75  | 69  | 66  | 82  | 74  | 69  | 66  | 73  | 69  | 65  |  | 72  | 68  | 65  |  | 71  |
| 9   | 80  | 71  | 66  | 62  | 79  | 71  | 66  | 62  | 70  | 65  | 62  |  | 69  | 65  | 62  |  | 68  |
| 10  | 77  | 68  | 62  | 59  | 76  | 67  | 62  | 59  | 67  | 62  | 59  |  | 66  | 62  | 59  |  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 93677 |
| 5°  | 90359 |
| 10° | 93585 |
| 15° | 92259 |
| 20° | 85384 |
| 25° | 69052 |
| 30° | 41373 |
| 35° | 14027 |
| 40° | 3864  |
| 45° | 1706  |
| 50° | 512   |
| 55° | 76    |
| 60° | 44    |
| 65° | 52    |
| 70° | 64    |
| 75° | 0     |
| 80° | 0     |
| 85° | 0     |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1706 cd/sqm

TEST NUMBER: P1253616

CATALOG NUMBER: P3AS02R559035DE010 E3D1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 39.7   | 12.3      |
| 10°-20°   | 113.2  | 35.0      |
| 20°-30°   | 125.8  | 38.9      |
| 30°-40°   | 39.2   | 12.1      |
| 40°-50°   | 4.7    | 1.5       |
| 50°-60°   | 0.3    | 0.1       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 278.6  | 86.3      |
| 0°-40°    | 317.8  | 98.4      |
| 0°-60°    | 322.8  | 100.0     |
| 0°-90°    | 323.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 323.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 427 |      |
| 5°  | 410 | 40   |
| 15° | 406 | 113  |
| 25° | 285 | 126  |
| 35° | 52  | 39   |
| 45° | 6   | 5    |
| 55° | 0   | 0    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1253616

CATALOG NUMBER: P3AS02R559035DE010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 427.2 |
| 1°    | 425.6 |
| 2°    | 421.4 |
| 3°    | 416.2 |
| 4°    | 411.6 |
| 5°    | 410.5 |
| 6°    | 411.7 |
| 7°    | 414.3 |
| 8°    | 417.2 |
| 9°    | 419.5 |
| 10°   | 420.3 |
| 11°   | 419.8 |
| 12°   | 417.8 |
| 13°   | 414.8 |
| 14°   | 411.2 |
| 15°   | 406.4 |
| 16°   | 400.9 |
| 17°   | 393.9 |
| 18°   | 386.0 |
| 19°   | 376.6 |
| 20°   | 365.9 |
| 21°   | 353.8 |
| 22°   | 339.4 |
| 23°   | 323.6 |
| 24°   | 305.4 |
| 25°   | 285.4 |
| 26°   | 263.5 |
| 27°   | 240.1 |
| 28°   | 215.2 |
| 29°   | 189.6 |
| 30°   | 163.4 |
| 31°   | 137.2 |
| 32°   | 111.5 |
| 32.5° | 100.1 |
| 33°   | 88.4  |
| 34°   | 68.3  |
| 35°   | 52.4  |
| 36°   | 39.9  |
| 37°   | 29.6  |
| 37.5° | 25.3  |
| 38°   | 22.0  |
| 39°   | 16.7  |
| 40°   | 13.5  |
| 42.5° | 8.6   |
| 45°   | 5.5   |



TEST NUMBER: P1253616

CATALOG NUMBER: P3AS02R559035DE010 E3D1LI

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 47.5° | 3.3 |
| 50°   | 1.5 |
| 52.5° | 0.5 |
| 55°   | 0.2 |
| 57.5° | 0.1 |
| 60°   | 0.1 |
| 62.5° | 0.1 |
| 65°   | 0.1 |
| 67.5° | 0.1 |
| 70°   | 0.1 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)