

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253620

Luminaire Tested: P3AS02R559035DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253620
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559035DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 134.0 lumens
Efficiency: N/A
Efficacy: 37.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253620

CATALOG NUMBER: P3AS02R559035DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1253620

CATALOG NUMBER: P3AS02R559035DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	95	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36795
5°	36430
10°	35181
15°	32509
20°	28049
25°	22163
30°	15724
35°	10146
40°	6097
45°	3442
50°	1842
55°	650
60°	614
65°	571
70°	577
75°	508
80°	505
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3442 cd/sqm

TEST NUMBER: P1253620

CATALOG NUMBER: P3AS02R559035DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.6	11.6
10°-20°	39.6	29.6
20°-30°	41.5	31.0
30°-40°	24.2	18.1
40°-50°	9.1	6.8
50°-60°	2.1	1.6
60°-70°	1.1	0.8
70°-80°	0.6	0.5
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	96.7	72.1
0°-40°	120.9	90.2
0°-60°	132.1	98.6
0°-90°	134.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	134.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	168	
5°	166	16
15°	143	40
25°	92	42
35°	38	24
45°	11	9
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1253620

CATALOG NUMBER: P3AS02R559035DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	167.8
2.5°	167.3
5°	165.5
7.5°	162.5
10°	158.0
12.5°	151.6
15°	143.2
17.5°	132.6
20°	120.2
22.5°	106.3
25°	91.6
27.5°	76.5
30°	62.1
32.5°	49.0
35°	37.9
37.5°	28.8
40°	21.3
42.5°	15.2
45°	11.1
47.5°	8.0
50°	5.4
52.5°	3.1
55°	1.7
57.5°	1.5
60°	1.4
62.5°	1.2
65°	1.1
67.5°	1.0
70°	0.9
72.5°	0.7
75°	0.6
77.5°	0.5
80°	0.4
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)