

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1254613

Luminaire Tested: P3AS13R209035DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1254613
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209035DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1035.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1254613
CATALOG NUMBER: P3AS13R209035DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1254613
 CATALOG NUMBER: P3AS13R209035DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	796318
5°	723859
10°	534993
15°	330944
20°	188993
25°	107885
30°	60516
35°	32926
40°	18034
45°	9924
50°	5799
55°	4205
60°	3947
65°	3632
70°	3206
75°	3389
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9924 cd/sqm



TEST NUMBER: P1254613
 CATALOG NUMBER: P3AS13R209035DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.8	27.5
10°-20°	406.5	39.3
20°-30°	212.2	20.5
30°-40°	82.1	7.9
40°-50°	26.6	2.6
50°-60°	10.5	1.0
60°-70°	6.9	0.7
70°-80°	4.1	0.4
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	903.5	87.3
0°-40°	985.5	95.2
0°-60°	1022.6	98.8
0°-90°	1035.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1035.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3632	
5°	3288	285
15°	1458	407
25°	446	212
35°	123	82
45°	32	27
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1254613
CATALOG NUMBER: P3AS13R209035DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3631.5
1°	3624.5
2°	3581.5
3°	3515.5
4°	3413.5
5°	3288.5
6°	3140.6
7°	2976.6
8°	2786.6
9°	2601.6
10°	2402.7
12.5°	1909.7
15°	1457.8
17.5°	1090.8
20°	809.9
22.5°	599.9
25°	445.9
27.5°	329.0
30°	239.0
32.5°	173.0
35°	123.0
37.5°	89.0
40°	63.0
42.5°	45.0
45°	32.0
47.5°	23.0
50°	17.0
52.5°	13.0
55°	11.0
57.5°	10.0
60°	9.0
62.5°	8.0
65°	7.0
67.5°	6.0
70°	5.0
72.5°	5.0
75°	4.0
77.5°	3.0
80°	2.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)